

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844041

Luminaire Tested: **LD6C15DE010B2750 EU6C15B30 6LBNLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B30 6LBNI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1202.5 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844041

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P844041

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150092
5°	140358
10°	114477
15°	84240
20°	58058
25°	43103
30°	32378
35°	20191
40°	9804
45°	3365
50°	443
55°	335
60°	186
65°	221
70°	272
75°	0
80°	0
85°	0



TEST NUMBER: P844041

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.6	18.9
10°-20°	408.6	34.0
20°-30°	330.3	27.5
30°-40°	190.3	15.8
40°-50°	40.2	3.3
50°-60°	3.5	0.3
60°-70°	1.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	966.6	80.4
0°-40°	1156.9	96.2
0°-60°	1200.6	99.8
0°-90°	1202.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1202.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2738	
5°	2551	228
15°	1484	409
25°	713	330
35°	302	190
45°	43	40
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844041

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2737.9
2.5°	2705.0
5°	2550.6
7.5°	2328.7
10°	2056.5
12.5°	1777.4
15°	1484.3
17.5°	1201.7
20°	995.2
22.5°	837.5
25°	712.6
27.5°	606.9
30°	511.5
32.5°	405.7
35°	301.7
37.5°	209.8
40°	137.0
42.5°	83.2
45°	43.4
47.5°	17.3
50°	5.2
52.5°	5.2
55°	3.5
57.5°	3.5
60°	1.7
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)