

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844054

Luminaire Tested: **LD6C15DE010B2750 EU6C15B35 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B35 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1134.9 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844054

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P844054

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61569
5°	60466
10°	57380
15°	53808
20°	50107
25°	46170
30°	38468
35°	27117
40°	17282
45°	10303
50°	6081
55°	3871
60°	2664
65°	1894
70°	1298
75°	1038
80°	505
85°	0



TEST NUMBER: P844054

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	9.0
10°-20°	265.7	23.4
20°-30°	344.2	30.3
30°-40°	255.5	22.5
40°-50°	107.9	9.5
50°-60°	38.3	3.4
60°-70°	14.8	1.3
70°-80°	5.1	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	712.6	62.8
0°-40°	968.1	85.3
0°-60°	1114.3	98.2
0°-90°	1134.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1134.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1123	
5°	1099	103
15°	948	266
25°	763	344
35°	405	256
45°	133	108
55°	40	38
65°	15	15
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P844054

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1123.1
2.5°	1119.8
5°	1098.8
7.5°	1068.0
10°	1030.8
12.5°	990.2
15°	948.1
17.5°	901.1
20°	858.9
22.5°	815.2
25°	763.3
27.5°	692.0
30°	607.7
32.5°	508.8
35°	405.2
37.5°	317.6
40°	241.5
42.5°	179.9
45°	132.9
47.5°	97.2
50°	71.3
52.5°	53.5
55°	40.5
57.5°	30.8
60°	24.3
62.5°	17.9
65°	14.6
67.5°	11.3
70°	8.1
72.5°	6.5
75°	4.9
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)