

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204500

Luminaire Tested: **LE_6B40D010 EC6B30508040 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508040 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4951.7 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204500
CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204500

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204500

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.2	4.2
10°-20°	585.0	11.8
20°-30°	870.2	17.6
30°-40°	1012.6	20.4
40°-50°	987.0	19.9
50°-60°	759.1	15.3
60°-70°	419.7	8.5
70°-80°	111.1	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1661.3	33.6
0°-40°	2673.9	54.0
0°-60°	4420.1	89.3
0°-90°	4951.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4951.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2184	
5°	2172	206
15°	2071	585
25°	1889	870
35°	1626	1013
45°	1280	987
55°	847	759
65°	420	420
75°	94	111
85°	0	1
90°	0	



TEST NUMBER: P204500

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2184.4
2.5°	2184.4
5°	2171.8
7.5°	2153.0
10°	2140.4
12.5°	2102.8
15°	2071.4
17.5°	2040.0
20°	1996.0
22.5°	1952.1
25°	1889.4
27.5°	1826.6
30°	1763.8
32.5°	1694.8
35°	1625.8
37.5°	1537.9
40°	1462.5
42.5°	1380.9
45°	1280.5
47.5°	1186.4
50°	1079.6
52.5°	966.6
55°	847.4
57.5°	734.4
60°	627.8
62.5°	521.0
65°	420.5
67.5°	326.4
70°	238.5
72.5°	163.2
75°	94.1
77.5°	44.0
80°	6.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)