

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844071

Luminaire Tested: **LD6C15DE010B2750 EU6C15B40 6LBMH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B40 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.4 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844071

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P844071

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60993
5°	59900
10°	56840
15°	53303
20°	49646
25°	45741
30°	38113
35°	26863
40°	17118
45°	10210
50°	6021
55°	3833
60°	2642
65°	1881
70°	1282
75°	1038
80°	505
85°	0



TEST NUMBER: P844071

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	9.0
10°-20°	263.2	23.4
20°-30°	341.0	30.3
30°-40°	253.2	22.5
40°-50°	106.9	9.5
50°-60°	37.9	3.4
60°-70°	14.7	1.3
70°-80°	5.1	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.9	62.8
0°-40°	959.1	85.3
0°-60°	1103.9	98.2
0°-90°	1124.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1113	
5°	1088	102
15°	939	263
25°	756	341
35°	401	253
45°	132	107
55°	40	38
65°	14	15
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P844071

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1112.6
2.5°	1109.4
5°	1088.5
7.5°	1058.1
10°	1021.1
12.5°	981.0
15°	939.2
17.5°	892.6
20°	851.0
22.5°	807.6
25°	756.2
27.5°	685.6
30°	602.1
32.5°	504.1
35°	401.4
37.5°	314.6
40°	239.2
42.5°	178.2
45°	131.7
47.5°	96.4
50°	70.6
52.5°	53.0
55°	40.1
57.5°	30.5
60°	24.1
62.5°	17.7
65°	14.5
67.5°	11.2
70°	8.0
72.5°	6.5
75°	4.9
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)