

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844103

Luminaire Tested: **LD6C20DE010B2750 EU6C20B27 6LBMB**

Issue Date: 5/7/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P844103  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C20DE010B2750 EU6C20B27 6LBMB  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 843.9 lumens  
Efficiency: N/A  
Efficacy: 38.7 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844103

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMB

### Luminous Intensity Polar Plot





TEST NUMBER: P844103

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34520
5°	34074
10°	32915
15°	31516
20°	29951
25°	27885
30°	24023
35°	18230
40°	13325
45°	10110
50°	8247
55°	7226
60°	6633
65°	6032
70°	5402
75°	4935
80°	4420
85°	3648



TEST NUMBER: P844103

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.2	6.9
10°-20°	155.8	18.5
20°-30°	209.2	24.8
30°-40°	171.6	20.3
40°-50°	103.1	12.2
50°-60°	68.5	8.1
60°-70°	45.9	5.4
70°-80°	24.7	2.9
80°-90°	7.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.2	50.1
0°-40°	594.9	70.5
0°-60°	766.4	90.8
0°-90°	843.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	630	
5°	619	58
15°	555	156
25°	461	209
35°	272	172
45°	130	103
55°	76	68
65°	46	46
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P844103

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	629.7
2.5°	625.1
5°	619.2
7.5°	606.4
10°	591.3
12.5°	572.7
15°	555.3
17.5°	534.3
20°	513.4
22.5°	490.1
25°	461.0
27.5°	426.0
30°	379.5
32.5°	327.1
35°	272.4
37.5°	225.8
40°	186.2
42.5°	154.8
45°	130.4
47.5°	110.6
50°	96.7
52.5°	84.9
55°	75.6
57.5°	67.5
60°	60.5
62.5°	52.4
65°	46.5
67.5°	39.6
70°	33.7
72.5°	27.9
75°	23.3
77.5°	18.6
80°	14.0
82.5°	10.5
85°	5.8
87.5°	2.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)