

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205532

Luminaire Tested: **LE_6B40D010 EC6B30509050 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509050 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2539.2 lumens
Efficiency: N/A
Efficacy: 60.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205532
CATALOG NUMBER: LE_6B40D010 EC6B30509050 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205532

CATALOG NUMBER: LE_6B40D010 EC6B30509050 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205532

CATALOG NUMBER: LE_6B40D010 EC6B30509050 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.1	9.6
10°-20°	630.8	24.8
20°-30°	803.7	31.7
30°-40°	567.9	22.4
40°-50°	207.3	8.2
50°-60°	57.5	2.3
60°-70°	20.8	0.8
70°-80°	7.4	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.5	66.1
0°-40°	2245.5	88.4
0°-60°	2510.3	98.9
0°-90°	2539.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2539.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2646	
5°	2600	243
15°	2246	631
25°	1784	804
35°	902	568
45°	251	207
55°	62	57
65°	20	21
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P205532

CATALOG NUMBER: LE_6B40D010 EC6B30509050 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2646.1
2.5°	2635.8
5°	2599.9
7.5°	2528.1
10°	2451.2
12.5°	2348.6
15°	2246.1
17.5°	2143.5
20°	2041.0
22.5°	1917.9
25°	1784.5
27.5°	1600.0
30°	1394.9
32.5°	1148.6
35°	902.5
37.5°	687.1
40°	502.5
42.5°	364.1
45°	251.2
47.5°	169.2
50°	112.9
52.5°	76.9
55°	61.5
57.5°	46.1
60°	35.9
62.5°	25.6
65°	20.5
67.5°	15.4
70°	10.2
72.5°	10.2
75°	5.1
77.5°	5.1
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)