

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203691

Luminaire Tested: **LE_6B50D010R EC6B30509024 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509024 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3036.7 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203691

CATALOG NUMBER: LE_6B50D010R EC6B30509024 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203691

CATALOG NUMBER: LE_6B50D010R EC6B30509024 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203691

CATALOG NUMBER: LE_6B50D010R EC6B30509024 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.1	11.5
10°-20°	834.8	27.5
20°-30°	956.4	31.5
30°-40°	642.6	21.2
40°-50°	183.6	6.0
50°-60°	44.9	1.5
60°-70°	17.0	0.6
70°-80°	6.5	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2141.3	70.5
0°-40°	2783.8	91.7
0°-60°	3012.4	99.2
0°-90°	3036.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3036.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3893	
5°	3782	350
15°	2996	835
25°	2088	956
35°	1024	643
45°	210	184
55°	50	45
65°	17	17
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P203691

CATALOG NUMBER: LE_6B50D010R EC6B30509024 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3892.8
2.5°	3865.1
5°	3782.0
7.5°	3632.5
10°	3449.8
12.5°	3217.2
15°	2995.8
17.5°	2763.1
20°	2530.6
22.5°	2309.1
25°	2087.6
27.5°	1882.8
30°	1644.6
32.5°	1329.0
35°	1024.4
37.5°	747.5
40°	515.0
42.5°	337.8
45°	210.4
47.5°	127.4
50°	77.5
52.5°	60.9
55°	49.9
57.5°	38.8
60°	27.6
62.5°	22.1
65°	16.6
67.5°	11.1
70°	11.1
72.5°	5.5
75°	5.5
77.5°	5.5
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)