

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203583

Luminaire Tested: **LE_6B50D010R EC6B30508027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5125.6 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203583

CATALOG NUMBER: LE_6B50D010R EC6B30508027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203583

CATALOG NUMBER: LE_6B50D010R EC6B30508027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 108 | 104 | 101 | 109 | 105 | 103 | 100 | 101 | 99 | 97 | 98 | 96 | 94 | 94 | 92 | 91 | 89 | | | |
| 2 | 104 | 97 | 92 | 88 | 101 | 96 | 91 | 87 | 92 | 88 | 85 | 89 | 86 | 83 | 86 | 83 | 81 | 79 | | | |
| 3 | 97 | 88 | 82 | 77 | 95 | 87 | 81 | 76 | 84 | 79 | 75 | 82 | 77 | 74 | 79 | 76 | 73 | 71 | | | |
| 4 | 90 | 81 | 74 | 68 | 88 | 80 | 73 | 68 | 77 | 72 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 64 | | | |
| 5 | 85 | 74 | 67 | 61 | 83 | 73 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 59 | 58 | | | |
| 6 | 79 | 68 | 61 | 56 | 78 | 68 | 61 | 56 | 66 | 60 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 | | | |
| 7 | 75 | 63 | 56 | 51 | 73 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 48 | | | |
| 8 | 70 | 59 | 52 | 47 | 69 | 58 | 51 | 47 | 57 | 51 | 46 | 56 | 50 | 46 | 55 | 50 | 46 | 44 | | | |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | |
| 10 | 63 | 51 | 45 | 40 | 62 | 51 | 44 | 40 | 50 | 44 | 40 | 49 | 44 | 40 | 48 | 43 | 40 | 38 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203583

CATALOG NUMBER: LE_6B50D010R EC6B30508027 6LBMMW1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 353.3 | 6.9 |
| 10°-20° | 946.3 | 18.5 |
| 20°-30° | 1270.7 | 24.8 |
| 30°-40° | 1042.3 | 20.3 |
| 40°-50° | 625.9 | 12.2 |
| 50°-60° | 415.9 | 8.1 |
| 60°-70° | 278.8 | 5.4 |
| 70°-80° | 150.0 | 2.9 |
| 80°-90° | 42.3 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2570.3 | 50.1 |
| 0°-40° | 3612.6 | 70.5 |
| 0°-60° | 4654.5 | 90.8 |
| 0°-90° | 5125.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5125.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3825 | |
| 5° | 3761 | 353 |
| 15° | 3372 | 946 |
| 25° | 2800 | 1271 |
| 35° | 1654 | 1042 |
| 45° | 792 | 626 |
| 55° | 460 | 416 |
| 65° | 283 | 279 |
| 75° | 141 | 150 |
| 85° | 35 | 42 |
| 90° | 0 | |



TEST NUMBER: P203583

CATALOG NUMBER: LE_6B50D010R EC6B30508027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3824.6 |
| 2.5° | 3796.2 |
| 5° | 3761.0 |
| 7.5° | 3683.2 |
| 10° | 3591.2 |
| 12.5° | 3478.1 |
| 15° | 3372.1 |
| 17.5° | 3244.9 |
| 20° | 3117.6 |
| 22.5° | 2976.2 |
| 25° | 2799.5 |
| 27.5° | 2587.4 |
| 30° | 2304.6 |
| 32.5° | 1986.5 |
| 35° | 1654.2 |
| 37.5° | 1371.5 |
| 40° | 1131.1 |
| 42.5° | 940.2 |
| 45° | 791.8 |
| 47.5° | 671.6 |
| 50° | 586.8 |
| 52.5° | 516.1 |
| 55° | 459.5 |
| 57.5° | 410.0 |
| 60° | 367.6 |
| 62.5° | 318.1 |
| 65° | 282.8 |
| 67.5° | 240.4 |
| 70° | 205.0 |
| 72.5° | 169.6 |
| 75° | 141.4 |
| 77.5° | 113.1 |
| 80° | 84.9 |
| 82.5° | 63.6 |
| 85° | 35.4 |
| 87.5° | 14.1 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)