

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844205

Luminaire Tested: **LD6C25DE010B2750 EU6C25B30 6LBMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C25DE010B2750 EU6C25B30 6LBMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1091.5 lumens
Efficiency: N/A
Efficacy: 36.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844205

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBMB

Luminous Intensity Polar Plot





TEST NUMBER: P844205

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44646
5°	44068
10°	42573
15°	40755
20°	38731
25°	36063
30°	31062
35°	23577
40°	17232
45°	13071
50°	10661
55°	9347
60°	8585
65°	7822
70°	7004
75°	6375
80°	5714
85°	4717



TEST NUMBER: P844205

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.2	6.9
10°-20°	201.5	18.5
20°-30°	270.6	24.8
30°-40°	221.9	20.3
40°-50°	133.3	12.2
50°-60°	88.6	8.1
60°-70°	59.4	5.4
70°-80°	32.0	2.9
80°-90°	9.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.3	50.1
0°-40°	769.3	70.5
0°-60°	991.1	90.8
0°-90°	1091.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	814	
5°	801	75
15°	718	202
25°	596	271
35°	352	222
45°	169	133
55°	98	89
65°	60	59
75°	30	32
85°	8	9
90°	0	



TEST NUMBER: P844205

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	814.4
2.5°	808.3
5°	800.8
7.5°	784.3
10°	764.8
12.5°	740.7
15°	718.1
17.5°	691.0
20°	663.9
22.5°	633.8
25°	596.2
27.5°	551.0
30°	490.7
32.5°	422.9
35°	352.3
37.5°	292.0
40°	240.8
42.5°	200.2
45°	168.6
47.5°	143.0
50°	125.0
52.5°	109.9
55°	97.8
57.5°	87.4
60°	78.3
62.5°	67.8
65°	60.3
67.5°	51.2
70°	43.7
72.5°	36.2
75°	30.1
77.5°	24.1
80°	18.1
82.5°	13.5
85°	7.5
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)