

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203589

Luminaire Tested: **LE_6B50D010R EC6B30509027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4401.3 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203589

CATALOG NUMBER: LE_6B50D010R EC6B30509027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203589

CATALOG NUMBER: LE_6B50D010R EC6B30509027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203589

CATALOG NUMBER: LE_6B50D010R EC6B30509027 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.4	6.9
10°-20°	812.6	18.5
20°-30°	1091.1	24.8
30°-40°	895.0	20.3
40°-50°	537.5	12.2
50°-60°	357.2	8.1
60°-70°	239.4	5.4
70°-80°	128.9	2.9
80°-90°	36.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2207.0	50.1
0°-40°	3102.0	70.5
0°-60°	3996.7	90.8
0°-90°	4401.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4401.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3284	
5°	3229	303
15°	2896	813
25°	2404	1091
35°	1420	895
45°	680	537
55°	395	357
65°	243	239
75°	121	129
85°	30	36
90°	0	



TEST NUMBER: P203589

CATALOG NUMBER: LE_6B50D010R EC6B30509027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3284.0
2.5°	3259.8
5°	3229.4
7.5°	3162.6
10°	3083.8
12.5°	2986.6
15°	2895.5
17.5°	2786.2
20°	2677.0
22.5°	2555.6
25°	2403.9
27.5°	2221.8
30°	1978.9
32.5°	1705.8
35°	1420.5
37.5°	1177.6
40°	971.2
42.5°	807.4
45°	679.9
47.5°	576.6
50°	503.9
52.5°	443.1
55°	394.6
57.5°	352.1
60°	315.6
62.5°	273.1
65°	242.9
67.5°	206.4
70°	176.0
72.5°	145.8
75°	121.4
77.5°	97.1
80°	72.9
82.5°	54.6
85°	30.4
87.5°	12.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)