

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204935

Luminaire Tested: **LE\_6B50D010R EC6B30509727 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204935  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509727 6LBCSMB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4428.9 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204935

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSCMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204935

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSCMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204935

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSCMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	4.0
10°-20°	503.9	11.4
20°-30°	757.6	17.1
30°-40°	898.9	20.3
40°-50°	889.5	20.1
50°-60°	698.7	15.8
60°-70°	391.7	8.8
70°-80°	110.0	2.5
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1438.4	32.5
0°-40°	2337.3	52.8
0°-60°	3925.4	88.6
0°-90°	4428.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4428.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1870	
5°	1867	177
15°	1788	504
25°	1645	758
35°	1442	899
45°	1159	889
55°	787	699
65°	390	392
75°	95	110
85°	0	2
90°	0	



TEST NUMBER: P204935

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSCMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1870.1
2.5°	1863.8
5°	1867.0
7.5°	1851.1
10°	1832.0
12.5°	1809.8
15°	1787.6
17.5°	1759.0
20°	1720.9
22.5°	1682.8
25°	1644.8
27.5°	1603.4
30°	1549.5
32.5°	1495.5
35°	1441.5
37.5°	1378.0
40°	1305.0
42.5°	1235.1
45°	1158.9
47.5°	1073.1
50°	984.2
52.5°	882.6
55°	787.4
57.5°	679.5
60°	577.9
62.5°	485.8
65°	390.5
67.5°	308.0
70°	228.6
72.5°	155.6
75°	95.2
77.5°	47.6
80°	12.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)