

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204822

Luminaire Tested: **LE_6B50D010R EC6B30508030 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508030 6LBSCMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7338.5 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204822

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSCMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204822

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSCMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204822

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSCMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.0	3.9
10°-20°	808.5	11.0
20°-30°	1216.2	16.6
30°-40°	1441.3	19.6
40°-50°	1434.4	19.5
50°-60°	1156.3	15.8
60°-70°	699.5	9.5
70°-80°	259.7	3.5
80°-90°	38.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2308.6	31.5
0°-40°	3749.9	51.1
0°-60°	6340.6	86.4
0°-90°	7338.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7338.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2997	
5°	2984	284
15°	2864	808
25°	2642	1216
35°	2308	1441
45°	1868	1434
55°	1290	1156
65°	703	699
75°	236	260
85°	31	39
90°	0	



TEST NUMBER: P204822

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSCMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2997.2
2.5°	2997.2
5°	2983.9
7.5°	2975.0
10°	2948.4
12.5°	2903.9
15°	2863.9
17.5°	2819.4
20°	2766.0
22.5°	2712.6
25°	2641.5
27.5°	2565.9
30°	2481.4
32.5°	2401.4
35°	2308.0
37.5°	2210.1
40°	2094.5
42.5°	1983.4
45°	1867.8
47.5°	1738.8
50°	1596.5
52.5°	1449.8
55°	1289.6
57.5°	1147.2
60°	987.2
62.5°	844.9
65°	702.6
67.5°	569.2
70°	444.8
72.5°	333.5
75°	235.6
77.5°	151.2
80°	89.0
82.5°	53.4
85°	31.1
87.5°	13.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)