

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204099

Luminaire Tested: **LE_6B50D010R EC6B30508030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508030 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4822.4 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204099

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204099

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204099

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.2	7.6
10°-20°	973.4	20.2
20°-30°	1299.6	26.9
30°-40°	1048.5	21.7
40°-50°	502.5	10.4
50°-60°	297.9	6.2
60°-70°	198.0	4.1
70°-80°	106.1	2.2
80°-90°	29.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2640.3	54.8
0°-40°	3688.8	76.5
0°-60°	4489.2	93.1
0°-90°	4822.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4822.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3955	
5°	3909	367
15°	3464	973
25°	2844	1300
35°	1678	1048
45°	621	502
55°	330	298
65°	199	198
75°	100	106
85°	23	29
90°	0	



TEST NUMBER: P204099

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3955.0
2.5°	3955.0
5°	3909.0
7.5°	3832.4
10°	3725.0
12.5°	3610.0
15°	3464.4
17.5°	3326.5
20°	3173.1
22.5°	3012.2
25°	2843.6
27.5°	2667.2
30°	2414.4
32.5°	2061.8
35°	1678.5
37.5°	1326.0
40°	1027.0
42.5°	797.1
45°	620.9
47.5°	490.5
50°	413.9
52.5°	367.9
55°	329.6
57.5°	298.9
60°	260.6
62.5°	230.0
65°	199.2
67.5°	168.6
70°	145.6
72.5°	122.6
75°	99.6
77.5°	76.6
80°	61.4
82.5°	46.0
85°	23.0
87.5°	7.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)