

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204408

Luminaire Tested: **LE_6B50D010R EC6B30508030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6384.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204408

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204408

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204408

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.2	4.4
10°-20°	783.6	12.3
20°-30°	1142.9	17.9
30°-40°	1303.4	20.4
40°-50°	1250.2	19.6
50°-60°	957.5	15.0
60°-70°	525.4	8.2
70°-80°	139.7	2.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2205.7	34.6
0°-40°	3509.1	55.0
0°-60°	5716.8	89.5
0°-90°	6384.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6384.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2965	
5°	2942	279
15°	2781	784
25°	2482	1143
35°	2084	1303
45°	1624	1250
55°	1073	958
65°	529	525
75°	123	140
85°	0	2
90°	0	



TEST NUMBER: P204408

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2965.0
2.5°	2957.4
5°	2942.1
7.5°	2919.1
10°	2888.5
12.5°	2834.9
15°	2781.1
17.5°	2719.9
20°	2650.9
22.5°	2566.6
25°	2482.4
27.5°	2398.1
30°	2290.9
32.5°	2191.2
35°	2084.0
37.5°	1976.8
40°	1869.5
42.5°	1754.5
45°	1624.2
47.5°	1494.0
50°	1356.1
52.5°	1210.5
55°	1072.6
57.5°	934.8
60°	789.1
62.5°	651.2
65°	528.6
67.5°	406.1
70°	298.8
72.5°	199.2
75°	122.6
77.5°	53.6
80°	15.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)