

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204202

Luminaire Tested: **LE_6B50D010R EC6B30508030 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508030 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6958.2 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204202

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204202

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204202

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.9	4.9
10°-20°	926.5	13.3
20°-30°	1286.7	18.5
30°-40°	1404.1	20.2
40°-50°	1309.8	18.8
50°-60°	994.2	14.3
60°-70°	544.4	7.8
70°-80°	149.7	2.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2554.0	36.7
0°-40°	3958.0	56.9
0°-60°	6262.0	90.0
0°-90°	6958.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6958.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3639	
5°	3608	341
15°	3302	926
25°	2796	1287
35°	2245	1404
45°	1701	1310
55°	1111	994
65°	544	544
75°	130	150
85°	0	2
90°	0	



TEST NUMBER: P204202

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3639.1
2.5°	3639.1
5°	3608.5
7.5°	3562.5
10°	3493.5
12.5°	3401.6
15°	3302.0
17.5°	3179.4
20°	3064.5
22.5°	2926.6
25°	2796.4
27.5°	2666.1
30°	2520.5
32.5°	2382.6
35°	2244.8
37.5°	2106.9
40°	1976.6
42.5°	1838.8
45°	1700.8
47.5°	1562.9
50°	1409.6
52.5°	1264.1
55°	1110.9
57.5°	965.4
60°	819.8
62.5°	674.2
65°	544.0
67.5°	421.4
70°	314.1
72.5°	214.5
75°	130.2
77.5°	61.2
80°	15.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)