

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202760

Luminaire Tested: **LE\_6B50D010R EC6B30508030 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202760  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30508030 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5909.4 lumens  
Efficiency: N/A  
Efficacy: 100.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202760

CATALOG NUMBER: LE\_6B50D010R EC6B30508030 6LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202760

CATALOG NUMBER: LE\_6B50D010R EC6B30508030 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202760

CATALOG NUMBER: LE\_6B50D010R EC6B30508030 6LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.3	5.8
10°-20°	976.8	16.5
20°-30°	1432.2	24.2
30°-40°	1490.6	25.2
40°-50°	1031.4	17.5
50°-60°	449.0	7.6
60°-70°	137.7	2.3
70°-80°	41.3	0.7
80°-90°	6.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2753.3	46.6
0°-40°	4243.9	71.8
0°-60°	5724.3	96.9
0°-90°	5909.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5909.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3645	
5°	3630	344
15°	3469	977
25°	3132	1432
35°	2412	1491
45°	1332	1031
55°	482	449
65°	130	138
75°	38	41
85°	8	6
90°	0	



TEST NUMBER: P202760

CATALOG NUMBER: LE\_6B50D010R EC6B30508030 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3644.9
2.5°	3652.6
5°	3629.6
7.5°	3599.0
10°	3560.6
12.5°	3522.4
15°	3468.8
17.5°	3399.9
20°	3323.2
22.5°	3239.1
25°	3131.9
27.5°	2994.0
30°	2817.9
32.5°	2634.1
35°	2412.1
37.5°	2167.0
40°	1883.8
42.5°	1600.4
45°	1332.4
47.5°	1079.8
50°	857.6
52.5°	650.9
55°	482.4
57.5°	344.6
60°	237.4
62.5°	176.1
65°	130.1
67.5°	99.5
70°	68.9
72.5°	53.6
75°	38.2
77.5°	23.0
80°	15.4
82.5°	7.6
85°	7.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)