

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844295

Luminaire Tested: **LD6C30DE010B2750 EU6C30B30 6LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B30 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1755.6 lumens
Efficiency: N/A
Efficacy: 51.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844295

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P844295

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123378
5°	120328
10°	111026
15°	98298
20°	85349
25°	73002
30°	60186
35°	39639
40°	21304
45°	9427
50°	3821
55°	2762
60°	1754
65°	1245
70°	1042
75°	678
80°	1010
85°	0



TEST NUMBER: P844295

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.4	11.5
10°-20°	482.6	27.5
20°-30°	552.9	31.5
30°-40°	371.5	21.2
40°-50°	106.1	6.0
50°-60°	26.0	1.5
60°-70°	9.9	0.6
70°-80°	3.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1237.9	70.5
0°-40°	1609.4	91.7
0°-60°	1741.5	99.2
0°-90°	1755.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1755.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2251	
5°	2187	202
15°	1732	483
25°	1207	553
35°	592	371
45°	122	106
55°	29	26
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P844295

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2250.6
2.5°	2234.6
5°	2186.6
7.5°	2100.0
10°	1994.5
12.5°	1860.0
15°	1732.0
17.5°	1597.6
20°	1463.0
22.5°	1334.9
25°	1206.9
27.5°	1088.4
30°	950.8
32.5°	768.3
35°	592.3
37.5°	432.1
40°	297.7
42.5°	195.2
45°	121.6
47.5°	73.6
50°	44.8
52.5°	35.2
55°	28.9
57.5°	22.4
60°	16.0
62.5°	12.8
65°	9.6
67.5°	6.5
70°	6.5
72.5°	3.2
75°	3.2
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)