

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205033

Luminaire Tested: **LE_6B50D010R EC6B30509030 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509030 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5868.6 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205033

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205033

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40		
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36		
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32		
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205033

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.0	4.3
10°-20°	712.6	12.1
20°-30°	1040.9	17.7
30°-40°	1190.5	20.3
40°-50°	1144.2	19.5
50°-60°	883.6	15.1
60°-70°	493.1	8.4
70°-80°	143.5	2.4
80°-90°	6.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2007.5	34.2
0°-40°	3198.0	54.5
0°-60°	5225.8	89.0
0°-90°	5868.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5868.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2695	
5°	2672	254
15°	2528	713
25°	2262	1041
35°	1906	1191
45°	1492	1144
55°	991	884
65°	494	493
75°	125	143
85°	4	6
90°	0	



TEST NUMBER: P205033

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2695.0
2.5°	2695.0
5°	2672.2
7.5°	2660.9
10°	2622.9
12.5°	2577.4
15°	2528.0
17.5°	2478.6
20°	2406.5
22.5°	2349.6
25°	2262.2
27.5°	2175.0
30°	2087.6
32.5°	2000.4
35°	1905.5
37.5°	1810.6
40°	1700.5
42.5°	1601.9
45°	1491.8
47.5°	1366.5
50°	1248.8
52.5°	1119.8
55°	990.8
57.5°	857.9
60°	732.6
62.5°	607.4
65°	493.5
67.5°	387.1
70°	288.5
72.5°	201.1
75°	125.2
77.5°	64.5
80°	22.8
82.5°	7.6
85°	3.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)