

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844296

Luminaire Tested: **LD6C30DE010B2750 EU6C30B30 6LBNLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B30 6LBNLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2218.9 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844296

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P844296

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276946
5°	258997
10°	211230
15°	155432
20°	107138
25°	79541
30°	59743
35°	37256
40°	18084
45°	6210
50°	810
55°	621
60°	351
65°	415
70°	513
75°	0
80°	0
85°	0



TEST NUMBER: P844296

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.0	18.9
10°-20°	753.9	34.0
20°-30°	609.6	27.5
30°-40°	351.1	15.8
40°-50°	74.2	3.3
50°-60°	6.4	0.3
60°-70°	3.2	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1783.5	80.4
0°-40°	2134.7	96.2
0°-60°	2215.3	99.8
0°-90°	2218.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2218.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5052	
5°	4706	420
15°	2739	754
25°	1315	610
35°	557	351
45°	80	74
55°	6	6
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844296

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5051.9
2.5°	4991.3
5°	4706.5
7.5°	4297.0
10°	3794.6
12.5°	3279.5
15°	2738.7
17.5°	2217.2
20°	1836.5
22.5°	1545.4
25°	1315.0
27.5°	1119.8
30°	943.8
32.5°	748.7
35°	556.7
37.5°	387.1
40°	252.7
42.5°	153.6
45°	80.1
47.5°	31.9
50°	9.5
52.5°	9.5
55°	6.5
57.5°	6.5
60°	3.2
62.5°	3.2
65°	3.2
67.5°	3.2
70°	3.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)