

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205038

Luminaire Tested: **LE_6B50D010R EC6B30509730 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509730 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5129.8 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205038

CATALOG NUMBER: LE_6B50D010R EC6B30509730 6LBSC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205038

CATALOG NUMBER: LE_6B50D010R EC6B30509730 6LBSC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205038

CATALOG NUMBER: LE_6B50D010R EC6B30509730 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.0	4.3
10°-20°	622.9	12.1
20°-30°	909.8	17.7
30°-40°	1040.6	20.3
40°-50°	1000.1	19.5
50°-60°	772.3	15.1
60°-70°	431.1	8.4
70°-80°	125.5	2.4
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.8	34.2
0°-40°	2795.4	54.5
0°-60°	4567.9	89.0
0°-90°	5129.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5129.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2356	
5°	2336	222
15°	2210	623
25°	1978	910
35°	1666	1041
45°	1304	1000
55°	866	772
65°	431	431
75°	110	125
85°	3	5
90°	0	



TEST NUMBER: P205038

CATALOG NUMBER: LE_6B50D010R EC6B30509730 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2355.8
2.5°	2355.8
5°	2335.8
7.5°	2325.9
10°	2292.6
12.5°	2252.9
15°	2209.8
17.5°	2166.6
20°	2103.5
22.5°	2053.8
25°	1977.5
27.5°	1901.1
30°	1824.9
32.5°	1748.5
35°	1665.6
37.5°	1582.6
40°	1486.4
42.5°	1400.1
45°	1303.9
47.5°	1194.5
50°	1091.6
52.5°	978.8
55°	866.0
57.5°	749.9
60°	640.4
62.5°	530.9
65°	431.4
67.5°	338.4
70°	252.1
72.5°	175.9
75°	109.5
77.5°	56.4
80°	19.9
82.5°	6.6
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)