

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844301

Luminaire Tested: **LD6C30DE010B2750 EU6C30B35 6LBCSMB**

Issue Date: 5/7/2024

Test Information

Test Method: LM-79-08
Report Number: P844301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B35 6LBCSMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2659.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844301

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P844301

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59540
5°	59492
10°	59462
15°	58899
20°	58473
25°	57892
30°	56907
35°	55974
40°	54316
45°	52478
50°	49337
55°	44672
60°	39207
65°	33013
70°	25838
75°	18110
80°	10165
85°	7045



TEST NUMBER: P844301

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	3.9
10°-20°	292.9	11.0
20°-30°	440.7	16.6
30°-40°	522.3	19.6
40°-50°	519.7	19.5
50°-60°	419.0	15.8
60°-70°	253.4	9.5
70°-80°	94.2	3.5
80°-90°	14.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	836.5	31.5
0°-40°	1358.7	51.1
0°-60°	2297.4	86.4
0°-90°	2659.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2659.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1086	
5°	1081	103
15°	1038	293
25°	957	441
35°	836	522
45°	677	520
55°	467	419
65°	254	253
75°	86	94
85°	11	14
90°	0	



TEST NUMBER: P844301

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBCSMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1086.1
2.5°	1086.1
5°	1081.1
7.5°	1078.0
10°	1068.2
12.5°	1052.0
15°	1037.8
17.5°	1021.6
20°	1002.3
22.5°	982.8
25°	957.1
27.5°	929.7
30°	899.0
32.5°	870.1
35°	836.4
37.5°	800.8
40°	759.0
42.5°	718.6
45°	676.9
47.5°	629.9
50°	578.5
52.5°	525.2
55°	467.4
57.5°	415.7
60°	357.6
62.5°	306.2
65°	254.5
67.5°	206.1
70°	161.2
72.5°	121.0
75°	85.5
77.5°	54.8
80°	32.2
82.5°	19.2
85°	11.2
87.5°	4.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)