

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204926

Luminaire Tested: **LE\_6B50D010R EC6B30508035 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204926  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30508035 6LBCSMB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6359.4 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204926

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBSCMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204926

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204926

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBSCMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	254.0	4.0
10°-20°	723.6	11.4
20°-30°	1087.8	17.1
30°-40°	1290.7	20.3
40°-50°	1277.3	20.1
50°-60°	1003.2	15.8
60°-70°	562.5	8.8
70°-80°	158.0	2.5
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2065.4	32.5
0°-40°	3356.1	52.8
0°-60°	5636.5	88.6
0°-90°	6359.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6359.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2685	
5°	2681	254
15°	2567	724
25°	2362	1088
35°	2070	1291
45°	1664	1277
55°	1131	1003
65°	561	562
75°	137	158
85°	0	2
90°	0	



TEST NUMBER: P204926

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2685.4
2.5°	2676.2
5°	2680.8
7.5°	2658.0
10°	2630.6
12.5°	2598.8
15°	2566.8
17.5°	2525.8
20°	2471.0
22.5°	2416.4
25°	2361.6
27.5°	2302.4
30°	2224.9
32.5°	2147.4
35°	2069.9
37.5°	1978.6
40°	1873.8
42.5°	1773.5
45°	1664.1
47.5°	1541.0
50°	1413.4
52.5°	1267.4
55°	1130.6
57.5°	975.6
60°	829.8
62.5°	697.5
65°	560.8
67.5°	442.2
70°	328.2
72.5°	223.4
75°	136.8
77.5°	68.4
80°	18.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)