

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844330

Luminaire Tested: **LD6C30DE010B2750 EU6C30B40 6LBNLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B40 6LBNLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2258.1 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844330

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B40 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P844330

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B40 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281836
5°	263564
10°	214954
15°	158179
20°	109023
25°	80938
30°	60794
35°	37912
40°	18406
45°	6311
50°	827
55°	631
60°	362
65°	428
70°	529
75°	0
80°	0
85°	0



TEST NUMBER: P844330

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B40 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.4	18.9
10°-20°	767.2	34.0
20°-30°	620.3	27.5
30°-40°	357.3	15.8
40°-50°	75.5	3.3
50°-60°	6.5	0.3
60°-70°	3.3	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1815.0	80.4
0°-40°	2172.3	96.2
0°-60°	2254.4	99.8
0°-90°	2258.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2258.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5141	
5°	4790	427
15°	2787	767
25°	1338	620
35°	566	357
45°	81	76
55°	7	7
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844330

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B40 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5141.1
2.5°	5079.3
5°	4789.5
7.5°	4372.7
10°	3861.5
12.5°	3337.4
15°	2787.1
17.5°	2256.4
20°	1868.8
22.5°	1572.6
25°	1338.1
27.5°	1139.6
30°	960.4
32.5°	761.9
35°	566.5
37.5°	394.0
40°	257.2
42.5°	156.3
45°	81.4
47.5°	32.6
50°	9.7
52.5°	9.7
55°	6.6
57.5°	6.6
60°	3.3
62.5°	3.3
65°	3.3
67.5°	3.3
70°	3.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)