

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203894

Luminaire Tested: **LE\_6B50D010R EC6B30508035 6LBNGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203894  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30508035 6LBNGPH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3446.6 lumens  
Efficiency: N/A  
Efficacy: 58.6 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203894

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBNGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203894

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBNGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203894

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBNGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	379.2	11.0
10°-20°	935.3	27.1
20°-30°	1133.3	32.9
30°-40°	772.3	22.4
40°-50°	183.9	5.3
50°-60°	28.8	0.8
60°-70°	10.7	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2447.8	71.0
0°-40°	3220.1	93.4
0°-60°	3432.8	99.6
0°-90°	3446.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3446.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4189	
5°	4072	379
15°	3348	935
25°	2476	1133
35°	1234	772
45°	196	184
55°	32	29
65°	8	11
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203894

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBNGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4189.4
2.5°	4165.8
5°	4071.5
7.5°	3945.8
10°	3764.9
12.5°	3560.5
15°	3348.4
17.5°	3128.2
20°	2908.1
22.5°	2688.1
25°	2475.9
27.5°	2279.4
30°	1996.4
32.5°	1627.0
35°	1234.0
37.5°	880.4
40°	581.6
42.5°	361.5
45°	196.5
47.5°	102.1
50°	55.0
52.5°	39.2
55°	31.5
57.5°	23.6
60°	15.8
62.5°	15.8
65°	7.9
67.5°	7.9
70°	7.9
72.5°	7.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)