

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203791

Luminaire Tested: **LE_6B50D010R EC6B30508035 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508035 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4616.4 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203791

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203791

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89		
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83		
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79		
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74		
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70		
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66		
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203791

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	767.2	16.6
10°-20°	1474.2	31.9
20°-30°	1340.2	29.0
30°-40°	812.4	17.6
40°-50°	184.9	4.0
50°-60°	23.6	0.5
60°-70°	10.7	0.2
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3581.7	77.6
0°-40°	4394.0	95.2
0°-60°	4602.6	99.7
0°-90°	4616.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4616.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9063	
5°	8545	767
15°	5309	1474
25°	2906	1340
35°	1288	812
45°	204	185
55°	24	24
65°	8	11
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203791

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9063.2
2.5°	8953.4
5°	8544.9
7.5°	7885.2
10°	7044.9
12.5°	6173.1
15°	5309.1
17.5°	4523.8
20°	3864.0
22.5°	3330.0
25°	2905.9
27.5°	2528.9
30°	2159.8
32.5°	1727.9
35°	1288.0
37.5°	903.1
40°	596.9
42.5°	369.1
45°	204.2
47.5°	94.2
50°	39.2
52.5°	31.4
55°	23.5
57.5°	23.5
60°	15.8
62.5°	15.8
65°	7.9
67.5°	7.9
70°	7.9
72.5°	7.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)