

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203173

Luminaire Tested: **LE_6B50D010R EC6B30508035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6476.9 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203173

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203173

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203173

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.5	5.3
10°-20°	960.6	14.8
20°-30°	1384.1	21.4
30°-40°	1437.0	22.2
40°-50°	1062.4	16.4
50°-60°	634.6	9.8
60°-70°	385.6	6.0
70°-80°	211.2	3.3
80°-90°	58.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2687.2	41.5
0°-40°	4124.2	63.7
0°-60°	5821.3	89.9
0°-90°	6476.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6476.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3637	
5°	3614	343
15°	3409	961
25°	3017	1384
35°	2318	1437
45°	1367	1062
55°	691	635
65°	385	386
75°	196	211
85°	47	59
90°	0	



TEST NUMBER: P203173

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3637.2
2.5°	3637.2
5°	3613.6
7.5°	3582.2
10°	3535.1
12.5°	3480.1
15°	3409.4
17.5°	3330.9
20°	3252.2
22.5°	3142.4
25°	3016.6
27.5°	2883.1
30°	2710.2
32.5°	2537.4
35°	2317.5
37.5°	2089.6
40°	1838.2
42.5°	1594.8
45°	1366.9
47.5°	1162.6
50°	982.0
52.5°	824.9
55°	691.4
57.5°	589.1
60°	502.8
62.5°	439.9
65°	384.9
67.5°	337.8
70°	290.6
72.5°	243.5
75°	196.4
77.5°	157.1
80°	117.9
82.5°	86.4
85°	47.1
87.5°	23.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)