

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205034

Luminaire Tested: **LE_6B50D010R EC6B30509035 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509035 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5952.7 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205034

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBSC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205034

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBSC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205034

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.6	4.3
10°-20°	722.8	12.1
20°-30°	1055.8	17.7
30°-40°	1207.6	20.3
40°-50°	1160.6	19.5
50°-60°	896.2	15.1
60°-70°	500.2	8.4
70°-80°	145.6	2.4
80°-90°	6.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2036.3	34.2
0°-40°	3243.9	54.5
0°-60°	5300.6	89.0
0°-90°	5952.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5952.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2734	
5°	2710	258
15°	2564	723
25°	2295	1056
35°	1933	1208
45°	1513	1161
55°	1005	896
65°	500	500
75°	127	146
85°	4	6
90°	0	



TEST NUMBER: P205034

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2733.6
2.5°	2733.6
5°	2710.5
7.5°	2699.0
10°	2660.5
12.5°	2614.2
15°	2564.2
17.5°	2514.1
20°	2441.0
22.5°	2383.2
25°	2294.8
27.5°	2206.1
30°	2117.6
32.5°	2029.0
35°	1932.8
37.5°	1836.5
40°	1724.9
42.5°	1624.8
45°	1513.1
47.5°	1386.0
50°	1266.8
52.5°	1135.8
55°	1004.9
57.5°	870.1
60°	743.1
62.5°	616.0
65°	500.5
67.5°	392.8
70°	292.6
72.5°	204.0
75°	127.0
77.5°	65.5
80°	23.1
82.5°	7.8
85°	3.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)