

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203591

Luminaire Tested: **LE_6B50D010R EC6B30509035 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509035 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4641.6 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203591

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203591

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 111 | 108 | 104 | 101 | 109 | 105 | 103 | 100 | 101 | 99 | 97 | 98 | 96 | 94 | 94 | 92 | 91 | 89 | | |
| 2 | 104 | 97 | 92 | 88 | 101 | 96 | 91 | 87 | 92 | 88 | 85 | 89 | 86 | 83 | 86 | 83 | 81 | 79 | | |
| 3 | 97 | 88 | 82 | 77 | 95 | 87 | 81 | 76 | 84 | 79 | 75 | 82 | 77 | 74 | 79 | 76 | 73 | 71 | | |
| 4 | 90 | 81 | 74 | 68 | 88 | 80 | 73 | 68 | 77 | 72 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 64 | | |
| 5 | 85 | 74 | 67 | 61 | 83 | 73 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 59 | 58 | | |
| 6 | 79 | 68 | 61 | 56 | 78 | 68 | 61 | 56 | 66 | 60 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 | | |
| 7 | 75 | 63 | 56 | 51 | 73 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 48 | | |
| 8 | 70 | 59 | 52 | 47 | 69 | 58 | 51 | 47 | 57 | 51 | 46 | 56 | 50 | 46 | 55 | 50 | 46 | 44 | | |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | |
| 10 | 63 | 51 | 45 | 40 | 62 | 51 | 44 | 40 | 50 | 44 | 40 | 49 | 44 | 40 | 48 | 43 | 40 | 38 | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203591

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBMMW1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 319.9 | 6.9 |
| 10°-20° | 857.0 | 18.5 |
| 20°-30° | 1150.7 | 24.8 |
| 30°-40° | 943.9 | 20.3 |
| 40°-50° | 566.8 | 12.2 |
| 50°-60° | 376.7 | 8.1 |
| 60°-70° | 252.5 | 5.4 |
| 70°-80° | 135.9 | 2.9 |
| 80°-90° | 38.3 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2327.6 | 50.1 |
| 0°-40° | 3271.5 | 70.5 |
| 0°-60° | 4215.0 | 90.8 |
| 0°-90° | 4641.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4641.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3464 | |
| 5° | 3406 | 320 |
| 15° | 3054 | 857 |
| 25° | 2535 | 1151 |
| 35° | 1498 | 944 |
| 45° | 717 | 567 |
| 55° | 416 | 377 |
| 65° | 256 | 252 |
| 75° | 128 | 136 |
| 85° | 32 | 38 |
| 90° | 0 | |



TEST NUMBER: P203591

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBMMW1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3463.5 |
| 2.5° | 3437.9 |
| 5° | 3405.9 |
| 7.5° | 3335.4 |
| 10° | 3252.1 |
| 12.5° | 3149.8 |
| 15° | 3053.8 |
| 17.5° | 2938.5 |
| 20° | 2823.2 |
| 22.5° | 2695.2 |
| 25° | 2535.1 |
| 27.5° | 2343.1 |
| 30° | 2087.0 |
| 32.5° | 1799.0 |
| 35° | 1498.0 |
| 37.5° | 1242.0 |
| 40° | 1024.2 |
| 42.5° | 851.5 |
| 45° | 717.0 |
| 47.5° | 608.1 |
| 50° | 531.4 |
| 52.5° | 467.4 |
| 55° | 416.1 |
| 57.5° | 371.4 |
| 60° | 332.9 |
| 62.5° | 288.1 |
| 65° | 256.1 |
| 67.5° | 217.6 |
| 70° | 185.6 |
| 72.5° | 153.6 |
| 75° | 128.0 |
| 77.5° | 102.4 |
| 80° | 76.9 |
| 82.5° | 57.6 |
| 85° | 32.0 |
| 87.5° | 12.8 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)