

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205236

Luminaire Tested: **LE_6B50D010R EC6B30509035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509035 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5848.5 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205236

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205236

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWL11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92											92																	
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83											83																	
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76											76																	
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69											69																	
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63											63																	
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57											57																	
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52											52																	
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48											48																	
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44											44																	
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41											41																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205236

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.5	6.0
10°-20°	1059.4	18.1
20°-30°	1597.0	27.3
30°-40°	1634.6	27.9
40°-50°	952.3	16.3
50°-60°	218.8	3.7
60°-70°	26.9	0.5
70°-80°	7.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3008.9	51.4
0°-40°	4643.5	79.4
0°-60°	5814.6	99.4
0°-90°	5848.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5848.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3654	
5°	3674	352
15°	3753	1059
25°	3501	1597
35°	2652	1635
45°	1227	952
55°	212	219
65°	20	27
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P205236

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	3653.6
2.5°	3647.0
5°	3673.6
7.5°	3700.1
10°	3733.2
12.5°	3739.9
15°	3753.1
17.5°	3739.9
20°	3706.8
22.5°	3600.6
25°	3501.1
27.5°	3342.0
30°	3136.5
32.5°	2924.2
35°	2652.4
37.5°	2347.4
40°	2009.2
42.5°	1631.2
45°	1226.8
47.5°	855.4
50°	563.6
52.5°	358.1
55°	212.2
57.5°	112.8
60°	59.6
62.5°	33.1
65°	19.9
67.5°	19.9
70°	13.2
72.5°	6.6
75°	6.6
77.5°	6.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)