

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844352

Luminaire Tested: **LD6C35DE010B2750 EU6C35B27 6LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C35DE010B2750 EU6C35B27 6LBCSMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3363.2 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844352

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B27 6LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P844352

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B27 6LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75317
5°	75253
10°	75216
15°	74501
20°	73961
25°	73226
30°	71986
35°	70805
40°	68700
45°	66379
50°	62412
55°	56495
60°	49590
65°	41755
70°	32682
75°	22897
80°	12817
85°	8932



TEST NUMBER: P844352

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B27 6LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	3.9
10°-20°	370.5	11.0
20°-30°	557.4	16.6
30°-40°	660.6	19.6
40°-50°	657.4	19.5
50°-60°	529.9	15.8
60°-70°	320.5	9.5
70°-80°	119.0	3.5
80°-90°	17.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.1	31.5
0°-40°	1718.7	51.1
0°-60°	2906.0	86.4
0°-90°	3363.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3363.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1374	
5°	1368	130
15°	1313	371
25°	1211	557
35°	1058	661
45°	856	657
55°	591	530
65°	322	321
75°	108	119
85°	14	18
90°	0	



TEST NUMBER: P844352

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B27 6LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1373.9
2.5°	1373.9
5°	1367.5
7.5°	1363.6
10°	1351.2
12.5°	1330.7
15°	1312.7
17.5°	1292.2
20°	1267.8
22.5°	1243.1
25°	1210.6
27.5°	1176.0
30°	1137.2
32.5°	1100.7
35°	1058.0
37.5°	1013.0
40°	960.0
42.5°	908.8
45°	856.2
47.5°	796.8
50°	731.8
52.5°	664.3
55°	591.1
57.5°	525.7
60°	452.3
62.5°	387.3
65°	321.9
67.5°	260.8
70°	203.9
72.5°	152.9
75°	108.1
77.5°	69.3
80°	40.6
82.5°	24.4
85°	14.2
87.5°	6.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)