

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203179

Luminaire Tested: **LE_6B50D010R EC6B30509035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5470.6 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203179

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203179

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203179

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.3	5.3
10°-20°	811.3	14.8
20°-30°	1169.0	21.4
30°-40°	1213.7	22.2
40°-50°	897.3	16.4
50°-60°	536.0	9.8
60°-70°	325.7	6.0
70°-80°	178.5	3.3
80°-90°	49.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2269.7	41.5
0°-40°	3483.4	63.7
0°-60°	4916.8	89.9
0°-90°	5470.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5470.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3072	
5°	3052	289
15°	2880	811
25°	2548	1169
35°	1957	1214
45°	1154	897
55°	584	536
65°	325	326
75°	166	178
85°	40	50
90°	0	



TEST NUMBER: P203179

CATALOG NUMBER: LE_6B50D010R EC6B30509035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3072.1
2.5°	3072.1
5°	3052.1
7.5°	3025.6
10°	2985.8
12.5°	2939.4
15°	2879.6
17.5°	2813.2
20°	2747.0
22.5°	2654.0
25°	2547.9
27.5°	2435.1
30°	2289.1
32.5°	2143.1
35°	1957.4
37.5°	1765.0
40°	1552.6
42.5°	1346.9
45°	1154.5
47.5°	982.0
50°	829.4
52.5°	696.8
55°	583.9
57.5°	497.6
60°	424.6
62.5°	371.6
65°	325.1
67.5°	285.2
70°	245.5
72.5°	205.8
75°	165.9
77.5°	132.8
80°	99.5
82.5°	73.0
85°	39.8
87.5°	19.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)