

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205332

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBNLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5502.8 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205332

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205332

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205332

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1041.7	18.9
10°-20°	1869.7	34.0
20°-30°	1511.7	27.5
30°-40°	870.9	15.8
40°-50°	184.1	3.3
50°-60°	15.9	0.3
60°-70°	7.8	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4423.0	80.4
0°-40°	5293.9	96.2
0°-60°	5493.9	99.8
0°-90°	5502.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5502.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12529	
5°	11672	###
15°	6792	1870
25°	3261	1512
35°	1381	871
45°	198	184
55°	16	16
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205332

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	12528.8
2.5°	12378.0
5°	11671.8
7.5°	10656.1
10°	9410.4
12.5°	8133.0
15°	6792.0
17.5°	5498.6
20°	4554.5
22.5°	3832.4
25°	3261.1
27.5°	2777.1
30°	2340.8
32.5°	1856.8
35°	1380.6
37.5°	960.1
40°	626.9
42.5°	380.9
45°	198.4
47.5°	79.4
50°	23.8
52.5°	23.8
55°	15.9
57.5°	15.9
60°	7.9
62.5°	7.9
65°	7.9
67.5°	7.9
70°	7.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)