

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202556

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7273.1 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202556

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202556

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																												
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77																												
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																												
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																												
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																												
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																												
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																												
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																												
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35																												
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202556

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.1	5.4
10°-20°	1017.2	14.0
20°-30°	1348.8	18.5
30°-40°	1438.6	19.8
40°-50°	1344.8	18.5
50°-60°	1025.4	14.1
60°-70°	557.8	7.7
70°-80°	149.6	2.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2755.1	37.9
0°-40°	4193.7	57.7
0°-60°	6563.9	90.2
0°-90°	7273.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7273.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4206	
5°	4148	389
15°	3627	1017
25°	2936	1349
35°	2299	1439
45°	1751	1345
55°	1154	1025
65°	557	558
75°	129	150
85°	0	2
90°	0	



TEST NUMBER: P202556

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4205.8
2.5°	4192.4
5°	4147.9
7.5°	4054.2
10°	3947.4
12.5°	3795.9
15°	3626.6
17.5°	3457.2
20°	3274.6
22.5°	3100.9
25°	2936.0
27.5°	2762.2
30°	2597.4
32.5°	2437.0
35°	2298.9
37.5°	2160.8
40°	2018.2
42.5°	1889.0
45°	1750.9
47.5°	1599.5
50°	1456.9
52.5°	1305.4
55°	1153.9
57.5°	989.1
60°	837.6
62.5°	695.0
65°	556.9
67.5°	432.1
70°	316.4
72.5°	218.2
75°	129.2
77.5°	57.9
80°	13.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)