

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205441

Luminaire Tested: **LE\_6B50D010R EC6B30509040 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205441  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509040 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6250.2 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205441  
CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205441

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89					89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68					68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60					60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47					47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43					43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39					39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36					36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33					33			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205441

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	363.5	5.8
10°-20°	925.3	14.8
20°-30°	1179.9	18.9
30°-40°	1223.6	19.6
40°-50°	1127.5	18.0
50°-60°	848.1	13.6
60°-70°	457.8	7.3
70°-80°	122.8	2.0
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2468.6	39.5
0°-40°	3692.2	59.1
0°-60°	5667.8	90.7
0°-90°	6250.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6250.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3944	
5°	3884	363
15°	3300	925
25°	2563	1180
35°	1952	1224
45°	1468	1127
55°	950	848
65°	458	458
75°	106	123
85°	0	2
90°	0	



TEST NUMBER: P205441

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3944.2
2.5°	3930.9
5°	3884.5
7.5°	3798.1
10°	3645.4
12.5°	3492.6
15°	3300.1
17.5°	3120.9
20°	2934.9
22.5°	2742.4
25°	2563.1
27.5°	2390.4
30°	2231.1
32.5°	2085.0
35°	1952.1
37.5°	1826.0
40°	1706.5
42.5°	1580.4
45°	1467.5
47.5°	1341.2
50°	1215.1
52.5°	1082.4
55°	949.5
57.5°	816.8
60°	690.6
62.5°	571.0
65°	458.1
67.5°	351.9
70°	259.0
72.5°	179.2
75°	106.2
77.5°	46.5
80°	13.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)