

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844465

Luminaire Tested: **LD6C40DE010B2750 EU6C40B30 6LBNH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B30 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3095.7 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844465

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P844465

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217543
5°	212161
10°	195766
15°	173321
20°	150490
25°	128723
30°	106124
35°	69881
40°	37570
45°	16630
50°	6746
55°	4865
60°	3081
65°	2205
70°	1811
75°	1207
80°	1799
85°	0



TEST NUMBER: P844465

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.9	11.5
10°-20°	851.0	27.5
20°-30°	974.9	31.5
30°-40°	655.0	21.2
40°-50°	187.1	6.0
50°-60°	45.8	1.5
60°-70°	17.4	0.6
70°-80°	6.8	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2182.8	70.5
0°-40°	2837.8	91.7
0°-60°	3070.8	99.2
0°-90°	3095.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3095.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3968	
5°	3855	357
15°	3054	851
25°	2128	975
35°	1044	655
45°	214	187
55°	51	46
65°	17	17
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P844465

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3968.3
2.5°	3940.2
5°	3855.4
7.5°	3703.0
10°	3516.8
12.5°	3279.6
15°	3053.9
17.5°	2816.9
20°	2579.6
22.5°	2354.0
25°	2128.1
27.5°	1919.2
30°	1676.5
32.5°	1354.7
35°	1044.2
37.5°	762.0
40°	525.0
42.5°	344.3
45°	214.5
47.5°	129.8
50°	79.1
52.5°	62.1
55°	50.9
57.5°	39.6
60°	28.1
62.5°	22.5
65°	17.0
67.5°	11.3
70°	11.3
72.5°	5.7
75°	5.7
77.5°	5.7
80°	5.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)