

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844466

Luminaire Tested: **LD6C40DE010B2750 EU6C40B30 6LBNLI**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844466  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C40DE010B2750 EU6C40B30 6LBNLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3913.3 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844466

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844466

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	488420
5°	456756
10°	372521
15°	274128
20°	188946
25°	140276
30°	105364
35°	65705
40°	31895
45°	10939
50°	1433
55°	1080
60°	625
65°	739
70°	914
75°	0
80°	0
85°	0



TEST NUMBER: P844466

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	740.8	18.9
10°-20°	1329.6	34.0
20°-30°	1075.0	27.5
30°-40°	619.3	15.8
40°-50°	130.9	3.3
50°-60°	11.3	0.3
60°-70°	5.7	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3145.4	80.4
0°-40°	3764.7	96.2
0°-60°	3906.9	99.8
0°-90°	3913.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3913.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8910	
5°	8300	741
15°	4830	1330
25°	2319	1075
35°	982	619
45°	141	131
55°	11	11
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P844466

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8909.5
2.5°	8802.5
5°	8300.2
7.5°	7577.9
10°	6692.1
12.5°	5783.7
15°	4830.1
17.5°	3910.4
20°	3238.8
22.5°	2725.4
25°	2319.1
27.5°	1974.9
30°	1664.5
32.5°	1320.5
35°	981.8
37.5°	682.7
40°	445.7
42.5°	270.9
45°	141.1
47.5°	56.4
50°	16.8
52.5°	16.8
55°	11.3
57.5°	11.3
60°	5.7
62.5°	5.7
65°	5.7
67.5°	5.7
70°	5.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)