

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204317

Luminaire Tested: **LE_6B60D010R EC6B60708027 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708027 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7477.7 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204317

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204317

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204317

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	411.3	5.5
10°-20°	1064.7	14.2
20°-30°	1392.6	18.6
30°-40°	1474.5	19.7
40°-50°	1375.3	18.4
50°-60°	1041.6	13.9
60°-70°	564.2	7.5
70°-80°	151.3	2.0
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2868.5	38.4
0°-40°	4343.0	58.1
0°-60°	6759.9	90.4
0°-90°	7477.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7477.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4460	
5°	4394	411
15°	3805	1065
25°	3028	1393
35°	2357	1475
45°	1792	1375
55°	1170	1042
65°	565	564
75°	131	151
85°	0	2
90°	0	



TEST NUMBER: P204317

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4459.6
2.5°	4443.2
5°	4394.2
7.5°	4287.9
10°	4148.8
12.5°	3985.0
15°	3805.0
17.5°	3600.5
20°	3420.4
22.5°	3215.9
25°	3027.6
27.5°	2839.5
30°	2659.4
32.5°	2504.0
35°	2356.6
37.5°	2209.4
40°	2070.2
42.5°	1931.1
45°	1792.0
47.5°	1636.6
50°	1481.1
52.5°	1325.6
55°	1170.1
57.5°	1006.5
60°	851.0
62.5°	703.8
65°	564.6
67.5°	433.8
70°	319.1
72.5°	220.9
75°	130.9
77.5°	57.2
80°	16.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)