

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203195

Luminaire Tested: **LE_6B60D010R EC6B60709727 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709727 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5039.9 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203195

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203195

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68		
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60		
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44		
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37		
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203195

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.5	5.3
10°-20°	747.5	14.8
20°-30°	1077.0	21.4
30°-40°	1118.2	22.2
40°-50°	826.7	16.4
50°-60°	493.8	9.8
60°-70°	300.1	6.0
70°-80°	164.4	3.3
80°-90°	45.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2091.0	41.5
0°-40°	3209.1	63.7
0°-60°	4529.7	89.9
0°-90°	5039.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5039.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2830	
5°	2812	267
15°	2653	747
25°	2347	1077
35°	1803	1118
45°	1064	827
55°	538	494
65°	300	300
75°	153	164
85°	37	46
90°	0	



TEST NUMBER: P203195

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2830.2
2.5°	2830.2
5°	2811.9
7.5°	2787.4
10°	2750.8
12.5°	2708.0
15°	2652.9
17.5°	2591.8
20°	2530.6
22.5°	2445.1
25°	2347.2
27.5°	2243.4
30°	2108.9
32.5°	1974.4
35°	1803.2
37.5°	1626.0
40°	1430.4
42.5°	1240.9
45°	1063.6
47.5°	904.6
50°	764.1
52.5°	641.9
55°	537.9
57.5°	458.5
60°	391.2
62.5°	342.4
65°	299.5
67.5°	262.9
70°	226.1
72.5°	189.5
75°	152.9
77.5°	122.2
80°	91.8
82.5°	67.2
85°	36.6
87.5°	18.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)