

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844495

Luminaire Tested: **LD6C40DE010B2750 EU6C40B40 6LBMGPH**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B40 6LBMGPH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2332.2 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844495

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B40 6LBMGPH

Luminous Intensity Polar Plot





TEST NUMBER: P844495

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B40 6LBMGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95393
5°	94161
10°	90952
15°	87078
20°	82753
25°	77043
30°	66371
35°	50373
40°	36826
45°	27925
50°	22780
55°	19985
60°	18332
65°	16694
70°	14954
75°	13619
80°	12186
85°	10127



TEST NUMBER: P844495

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B40 6LBMGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	6.9
10°-20°	430.6	18.5
20°-30°	578.1	24.8
30°-40°	474.2	20.3
40°-50°	284.8	12.2
50°-60°	189.3	8.1
60°-70°	126.9	5.4
70°-80°	68.3	2.9
80°-90°	19.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.4	50.1
0°-40°	1643.7	70.5
0°-60°	2117.7	90.8
0°-90°	2332.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2332.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1740	
5°	1711	161
15°	1534	431
25°	1274	578
35°	753	474
45°	360	285
55°	209	189
65°	129	127
75°	64	68
85°	16	19
90°	0	



TEST NUMBER: P844495

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B40 6LBMGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1740.1
2.5°	1727.2
5°	1711.1
7.5°	1675.8
10°	1633.9
12.5°	1582.4
15°	1534.3
17.5°	1476.4
20°	1418.5
22.5°	1354.2
25°	1273.7
27.5°	1177.3
30°	1048.5
32.5°	903.7
35°	752.7
37.5°	624.0
40°	514.6
42.5°	427.8
45°	360.2
47.5°	305.6
50°	267.1
52.5°	234.8
55°	209.1
57.5°	186.6
60°	167.2
62.5°	144.8
65°	128.7
67.5°	109.4
70°	93.3
72.5°	77.2
75°	64.3
77.5°	51.4
80°	38.6
82.5°	29.0
85°	16.1
87.5°	6.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)