

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203906

Luminaire Tested: **LE_6B60D010R EC6B60708030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708030 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3754.4 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203906

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203906

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203906

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.1	11.0
10°-20°	1018.9	27.1
20°-30°	1234.5	32.9
30°-40°	841.3	22.4
40°-50°	200.3	5.3
50°-60°	31.3	0.8
60°-70°	11.6	0.3
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2666.6	71.0
0°-40°	3507.9	93.4
0°-60°	3739.5	99.6
0°-90°	3754.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3754.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4564	
5°	4435	413
15°	3648	1019
25°	2697	1235
35°	1344	841
45°	214	200
55°	34	31
65°	8	12
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203906

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4563.8
2.5°	4538.1
5°	4435.4
7.5°	4298.4
10°	4101.4
12.5°	3878.8
15°	3647.6
17.5°	3407.9
20°	3168.1
22.5°	2928.4
25°	2697.1
27.5°	2483.1
30°	2174.9
32.5°	1772.4
35°	1344.2
37.5°	959.0
40°	633.6
42.5°	393.9
45°	214.0
47.5°	111.2
50°	59.9
52.5°	42.8
55°	34.2
57.5°	25.6
60°	17.1
62.5°	17.1
65°	8.5
67.5°	8.5
70°	8.5
72.5°	8.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)