

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204421

Luminaire Tested: **LE_6B60D010R EC6B60708030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7132.9 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204421

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204421

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204421

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.9	4.4
10°-20°	875.6	12.3
20°-30°	1277.0	17.9
30°-40°	1456.2	20.4
40°-50°	1396.9	19.6
50°-60°	1069.8	15.0
60°-70°	587.1	8.2
70°-80°	156.1	2.2
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2464.4	34.6
0°-40°	3920.7	55.0
0°-60°	6387.4	89.5
0°-90°	7132.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7132.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3313	
5°	3287	312
15°	3107	876
25°	2774	1277
35°	2328	1456
45°	1815	1397
55°	1198	1070
65°	591	587
75°	137	156
85°	0	2
90°	0	



TEST NUMBER: P204421

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3312.9
2.5°	3304.2
5°	3287.1
7.5°	3261.5
10°	3227.2
12.5°	3167.4
15°	3107.4
17.5°	3038.9
20°	2961.9
22.5°	2867.8
25°	2773.5
27.5°	2679.4
30°	2559.5
32.5°	2448.2
35°	2328.4
37.5°	2208.6
40°	2088.8
42.5°	1960.4
45°	1814.8
47.5°	1669.2
50°	1515.1
52.5°	1352.5
55°	1198.5
57.5°	1044.4
60°	881.8
62.5°	727.6
65°	590.6
67.5°	453.8
70°	333.9
72.5°	222.6
75°	137.0
77.5°	59.9
80°	17.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)