

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205248

Luminaire Tested: **LE_6B60D010R EC6B60709030 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709030 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6442.1 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205248

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBWL11

Luminous Intensity Polar Plot






TEST NUMBER: P205248

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBWL11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205248

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.3	6.0
10°-20°	1167.0	18.1
20°-30°	1759.1	27.3
30°-40°	1800.5	27.9
40°-50°	1048.9	16.3
50°-60°	241.0	3.7
60°-70°	29.6	0.5
70°-80°	7.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3314.4	51.4
0°-40°	5114.9	79.4
0°-60°	6404.9	99.4
0°-90°	6442.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6442.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4025	
5°	4046	388
15°	4134	1167
25°	3857	1759
35°	2922	1801
45°	1351	1049
55°	234	241
65°	22	30
75°	7	8
85°	0	0
90°	0	



TEST NUMBER: P205248

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBWL11

CANDELA DISTRIBUTION (FULL):

0°	
0°	4024.6
2.5°	4017.2
5°	4046.5
7.5°	4075.8
10°	4112.2
12.5°	4119.5
15°	4134.1
17.5°	4119.5
20°	4083.0
22.5°	3966.1
25°	3856.6
27.5°	3681.2
30°	3454.9
32.5°	3221.1
35°	2921.6
37.5°	2585.6
40°	2213.1
42.5°	1796.9
45°	1351.2
47.5°	942.2
50°	620.9
52.5°	394.4
55°	233.8
57.5°	124.1
60°	65.8
62.5°	36.5
65°	21.9
67.5°	21.9
70°	14.6
72.5°	7.2
75°	7.2
77.5°	7.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)