

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205152

Luminaire Tested: **LE_6B60D010R EC6B60709730 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709730 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4986.3 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205152

CATALOG NUMBER: LE_6B60D010R EC6B60709730 6LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P205152

CATALOG NUMBER: LE_6B60D010R EC6B60709730 6LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																												
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																												
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																												
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																												
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																												
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																												
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																												
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																												
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																												
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205152

CATALOG NUMBER: LE_6B60D010R EC6B60709730 6LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	574.9	11.5
10°-20°	1431.2	28.7
20°-30°	1663.7	33.4
30°-40°	1018.8	20.4
40°-50°	253.0	5.1
50°-60°	29.6	0.6
60°-70°	11.0	0.2
70°-80°	4.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3669.8	73.6
0°-40°	4688.6	94.0
0°-60°	4971.1	99.7
0°-90°	4986.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4986.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6240	
5°	6157	575
15°	5136	1431
25°	3682	1664
35°	1595	1019
45°	281	253
55°	26	30
65°	13	11
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P205152

CATALOG NUMBER: LE_6B60D010R EC6B60709730 6LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6240.2
2.5°	6233.9
5°	6157.2
7.5°	5991.4
10°	5768.0
12.5°	5474.5
15°	5136.4
17.5°	4772.6
20°	4415.4
22.5°	4058.0
25°	3681.6
27.5°	3247.8
30°	2750.0
32.5°	2169.4
35°	1595.1
37.5°	1123.0
40°	765.6
42.5°	478.5
45°	280.8
47.5°	159.5
50°	83.0
52.5°	38.2
55°	25.5
57.5°	19.1
60°	19.1
62.5°	12.8
65°	12.8
67.5°	6.4
70°	6.4
72.5°	6.4
75°	6.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)