

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843850

Luminaire Tested: **LD6C08DE010B2750 EU6C08B27 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B2750 EU6C08B27 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 608.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843850

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B27 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843850

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B27 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32996
5°	32401
10°	30750
15°	28831
20°	26853
25°	24739
30°	20611
35°	14529
40°	9253
45°	5520
50°	3258
55°	2074
60°	1425
65°	1012
70°	689
75°	551
80°	253
85°	0



TEST NUMBER: P843850

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B27 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	9.1
10°-20°	142.4	23.4
20°-30°	184.4	30.3
30°-40°	136.9	22.5
40°-50°	57.8	9.5
50°-60°	20.5	3.4
60°-70°	7.9	1.3
70°-80°	2.8	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.8	62.8
0°-40°	518.8	85.3
0°-60°	597.1	98.2
0°-90°	608.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	608.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	589	55
15°	508	142
25°	409	184
35°	217	137
45°	71	58
55°	22	21
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P843850

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B27 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	601.9
2.5°	600.1
5°	588.8
7.5°	572.3
10°	552.4
12.5°	530.6
15°	508.0
17.5°	482.9
20°	460.3
22.5°	436.8
25°	409.0
27.5°	370.8
30°	325.6
32.5°	272.7
35°	217.1
37.5°	170.2
40°	129.3
42.5°	96.4
45°	71.2
47.5°	52.1
50°	38.2
52.5°	28.7
55°	21.7
57.5°	16.5
60°	13.0
62.5°	9.5
65°	7.8
67.5°	6.0
70°	4.3
72.5°	3.5
75°	2.6
77.5°	1.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)