

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203289

Luminaire Tested: **LE_6B60D010R EC6B60708035 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708035 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5596.5 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203289

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203289

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			100																	
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			92																	
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			85																	
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																			78																	
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			72																	
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			66																	
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			61																	
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			57																	
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			53																	
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			49																	
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			46																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203289

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	506.4	9.0
10°-20°	1310.0	23.4
20°-30°	1697.4	30.3
30°-40°	1260.2	22.5
40°-50°	532.0	9.5
50°-60°	189.0	3.4
60°-70°	72.9	1.3
70°-80°	25.3	0.5
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3513.9	62.8
0°-40°	4774.1	85.3
0°-60°	5495.0	98.2
0°-90°	5596.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5596.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5538	
5°	5418	506
15°	4675	1310
25°	3764	1697
35°	1998	1260
45°	655	532
55°	200	189
65°	72	73
75°	24	25
85°	0	3
90°	0	



TEST NUMBER: P203289

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5538.2
2.5°	5522.4
5°	5418.4
7.5°	5266.6
10°	5082.8
12.5°	4883.0
15°	4675.2
17.5°	4443.4
20°	4235.6
22.5°	4019.9
25°	3764.1
27.5°	3412.5
30°	2996.9
32.5°	2509.4
35°	1998.0
37.5°	1566.4
40°	1190.8
42.5°	887.1
45°	655.4
47.5°	479.5
50°	351.6
52.5°	263.8
55°	199.8
57.5°	151.9
60°	119.9
62.5°	87.9
65°	71.9
67.5°	56.0
70°	40.0
72.5°	32.0
75°	24.0
77.5°	16.0
80°	8.0
82.5°	8.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)