

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205143

Luminaire Tested: **LE\_6B60D010R EC6B60708040 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205143  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60708040 6LBML1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6919.0 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205143

CATALOG NUMBER: LE\_6B60D010R EC6B60708040 6LBML11

### Luminous Intensity Polar Plot





TEST NUMBER: P205143

CATALOG NUMBER: LE\_6B60D010R EC6B60708040 6LBML11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205143

CATALOG NUMBER: LE\_6B60D010R EC6B60708040 6LBML11

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	797.7	11.5
10°-20°	1985.9	28.7
20°-30°	2308.5	33.4
30°-40°	1413.7	20.4
40°-50°	351.0	5.1
50°-60°	41.0	0.6
60°-70°	15.3	0.2
70°-80°	5.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5092.1	73.6
0°-40°	6505.8	94.0
0°-60°	6897.8	99.7
0°-90°	6919.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6919.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8659	
5°	8544	798
15°	7127	1986
25°	5108	2309
35°	2213	1414
45°	390	351
55°	35	41
65°	18	15
75°	9	6
85°	0	0
90°	0	



TEST NUMBER: P205143

CATALOG NUMBER: LE\_6B60D010R EC6B60708040 6LBML11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8658.9
2.5°	8650.0
5°	8543.8
7.5°	8313.5
10°	8003.6
12.5°	7596.4
15°	7127.1
17.5°	6622.5
20°	6126.8
22.5°	5630.9
25°	5108.5
27.5°	4506.5
30°	3815.9
32.5°	3010.2
35°	2213.4
37.5°	1558.2
40°	1062.4
42.5°	664.0
45°	389.5
47.5°	221.4
50°	115.1
52.5°	53.1
55°	35.4
57.5°	26.5
60°	26.5
62.5°	17.8
65°	17.8
67.5°	8.9
70°	8.9
72.5°	8.9
75°	8.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)