

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203805

Luminaire Tested: **LE_6B60D010R EC6B60708040 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708040 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5209.2 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203805
CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203805

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203805

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	865.7	16.6
10°-20°	1663.6	31.9
20°-30°	1512.3	29.0
30°-40°	916.7	17.6
40°-50°	208.7	4.0
50°-60°	26.6	0.5
60°-70°	12.1	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4041.6	77.6
0°-40°	4958.3	95.2
0°-60°	5193.7	99.7
0°-90°	5209.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5209.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10227	
5°	9642	866
15°	5991	1664
25°	3279	1512
35°	1453	917
45°	230	209
55°	27	27
65°	9	12
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203805

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	10227.1
2.5°	10103.1
5°	9642.2
7.5°	8897.9
10°	7949.5
12.5°	6965.9
15°	5991.0
17.5°	5104.8
20°	4360.2
22.5°	3757.6
25°	3279.1
27.5°	2853.6
30°	2437.1
32.5°	1949.8
35°	1453.4
37.5°	1019.1
40°	673.5
42.5°	416.5
45°	230.4
47.5°	106.4
50°	44.2
52.5°	35.5
55°	26.6
57.5°	26.6
60°	17.8
62.5°	17.8
65°	8.9
67.5°	8.9
70°	8.9
72.5°	8.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)