

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202569

Luminaire Tested: **LE_6B60D010R EC6B60708040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8126.2 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202569

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202569

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35																			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202569

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.8	5.4
10°-20°	1136.5	14.0
20°-30°	1507.0	18.5
30°-40°	1607.4	19.8
40°-50°	1502.5	18.5
50°-60°	1145.7	14.1
60°-70°	623.2	7.7
70°-80°	167.2	2.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3078.2	37.9
0°-40°	4685.6	57.7
0°-60°	7333.8	90.2
0°-90°	8126.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8126.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4699	
5°	4634	435
15°	4052	1136
25°	3280	1507
35°	2569	1607
45°	1956	1503
55°	1289	1146
65°	622	623
75°	144	167
85°	0	2
90°	0	



TEST NUMBER: P202569

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4699.1
2.5°	4684.1
5°	4634.4
7.5°	4529.9
10°	4410.4
12.5°	4241.1
15°	4052.0
17.5°	3862.9
20°	3658.8
22.5°	3464.6
25°	3280.4
27.5°	3086.2
30°	2902.1
32.5°	2722.9
35°	2568.6
37.5°	2414.2
40°	2255.0
42.5°	2110.6
45°	1956.2
47.5°	1787.0
50°	1627.8
52.5°	1458.5
55°	1289.2
57.5°	1105.1
60°	935.9
62.5°	776.5
65°	622.2
67.5°	482.9
70°	353.4
72.5°	243.9
75°	144.4
77.5°	64.8
80°	14.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)