

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205557

Luminaire Tested: **LE_6B60D010R EC6B60709040 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709040 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3614.1 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205557

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205557

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																																				
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																																				
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																																				
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																																				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																																				
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																																				
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																																				
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																																				
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																																				
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205557

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.0	9.6
10°-20°	897.8	24.8
20°-30°	1143.9	31.7
30°-40°	808.4	22.4
40°-50°	295.1	8.2
50°-60°	81.8	2.3
60°-70°	29.7	0.8
70°-80°	10.5	0.3
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2387.6	66.1
0°-40°	3196.0	88.4
0°-60°	3573.0	98.9
0°-90°	3614.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3614.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3766	
5°	3700	346
15°	3197	898
25°	2540	1144
35°	1285	808
45°	358	295
55°	88	82
65°	29	30
75°	7	11
85°	0	1
90°	0	



TEST NUMBER: P205557

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3766.1
2.5°	3751.5
5°	3700.4
7.5°	3598.2
10°	3488.8
12.5°	3342.8
15°	3196.9
17.5°	3050.9
20°	2904.9
22.5°	2729.8
25°	2540.0
27.5°	2277.2
30°	1985.2
32.5°	1634.9
35°	1284.6
37.5°	978.0
40°	715.2
42.5°	518.2
45°	357.6
47.5°	240.9
50°	160.6
52.5°	109.5
55°	87.6
57.5°	65.8
60°	51.1
62.5°	36.5
65°	29.2
67.5°	21.9
70°	14.6
72.5°	14.6
75°	7.2
77.5°	7.2
80°	7.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)