

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204321

Luminaire Tested: **LE\_6B60D010R EC6B60708050 6LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204321  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60708050 6LBSWH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8092.7 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204321

CATALOG NUMBER: LE\_6B60D010R EC6B60708050 6LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204321

CATALOG NUMBER: LE\_6B60D010R EC6B60708050 6LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204321

CATALOG NUMBER: LE\_6B60D010R EC6B60708050 6LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	445.1	5.5
10°-20°	1152.2	14.2
20°-30°	1507.1	18.6
30°-40°	1595.8	19.7
40°-50°	1488.4	18.4
50°-60°	1127.3	13.9
60°-70°	610.6	7.5
70°-80°	163.8	2.0
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3104.4	38.4
0°-40°	4700.2	58.1
0°-60°	7315.9	90.4
0°-90°	8092.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8092.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4826	
5°	4756	445
15°	4118	1152
25°	3277	1507
35°	2550	1596
45°	1939	1488
55°	1266	1127
65°	611	611
75°	142	164
85°	0	2
90°	0	



TEST NUMBER: P204321

CATALOG NUMBER: LE\_6B60D010R EC6B60708050 6LBSWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4826.4
2.5°	4808.8
5°	4755.6
7.5°	4640.5
10°	4489.9
12.5°	4312.8
15°	4118.0
17.5°	3896.5
20°	3701.8
22.5°	3480.4
25°	3276.6
27.5°	3073.0
30°	2878.1
32.5°	2709.9
35°	2550.5
37.5°	2391.1
40°	2240.5
42.5°	2090.0
45°	1939.4
47.5°	1771.1
50°	1602.9
52.5°	1434.6
55°	1266.4
57.5°	1089.2
60°	921.0
62.5°	761.6
65°	611.0
67.5°	469.4
70°	345.4
72.5°	239.1
75°	141.8
77.5°	62.0
80°	17.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)